



WRAPPING

CAR CARE - DETAILING

WINDOWS TINTING

PPF

A close-up photograph of a brown, textured tool handle. The word "MODULO" is printed in large, white, bold, sans-serif capital letters on the handle. The background is blurred, showing what appears to be a workshop or garage setting with various tools and equipment.

MODULO

YOUR PERSONAL ASSISTANT

MODULO

EQUIPMENT AND USE



YOUR PERSONAL ASSISTANT

MODULO



FEATURES

Car wrapping, car detailing, PPF, window tint and other related activities require specific and different equipment, not always available simultaneously and usable in a practical and fast way by the operator.

This is why OXY TOOLS has studied "MODULO", a mobile support capable of being functional to different activities thanks to its modularity obtainable by mounting and removing specific accessories.

Made of hydrophobic material and dyed in its thickness, it is resistant to splashes of water and makes scratches and signs of wear almost invisible.

On "MODULO" everything finds its place: heat-gun, sprayers, cutting wires, paper roll, tape, electric cables extension and so on, thanks to dedicated housings, to the two large and divisible drawers and to the removability of the upper part of the structure.

The shapes and dimensions guarantee an excellent compromise between capacity and movement of the structure within the work centers.

Working with "MODULO" on your side means having the necessary equipment immediately available, reducing what we have to "wear", increasing comfort, quality, profitability and reducing work times.

"MODULO" is a customizable product, in fact in addition to the many types of equipment obtainable with OXY accessories, the user can easily apply hooks, plates, supports and more simply by inserting threaded bushes, available as accessories, into the structure.

The possibility of electrifying MODULO through the application of a 220V industrial socket connected to a power strip (Shuko, USB) further increases its functionalities and fields of use, transforming it into a work station to which to directly connect polishing machines, sanders, heat-gun, lamps and much more.

DIMENSIONS AND WEIGHTS:

Width 780 mm

Total height 1540 mm (with wheels)


Base height 840 mm

Height of superstructure 600 mm

Total weight with accessories supplied 38 kg

PRESENTATION VIDEO: <https://www.oxytools.it/products/modulo/?lang=en>

ACCESSORIES



electrical cable holder



big tub



infrared hook



small tubs (pair)



magnet plate



orbital holder plate



knife less plate



ELETRIFICATION

MODULO is supplied with the predisposition for the assembly of the industrial socket and the multiple socket schuko. The possibility of electrifying "MODULO" through the application of a 220V industrial socket connected to a power strip (Schuko, USB) further increases its functionality and fields of use by transforming it into a work station to which to directly connect polishers, sanders, heat gun, infrared lamps and much more.



Industrial socket positioning provided.
Hole for electric wire passage



Compartment for inserting multi-socket schuko.
We recommend using a socket with 3 outlets to leave the necessary space for the STORM TANK pipes



ASSEMBLING ACCESSORIES

MODULO is delivered with the predisposition to mount the side plate applicable on the side of the superstructure and with the holes for the mobility of the hooks.
For the assembly of other OXY accessories of current or future production, please proceed as follows:

- Remove the threaded bushings from the hardware bag.
- Place the object to be applied to the MODULE on the surface and mark the fixing points with a pencil / marker.
- Drill 8mm holes 10mm deep, NOT THROUGH!
- Insert the bushes by screwing them into the hole made DO NOT FORCE!
- Position the accessory to be mounted and tighten the flat head screws by performing a MODERATE clamping force.



ASSEMBLY


Module is delivered assembled and ready for use. For transport reasons, the only components that are not fitted are the wheels.

The 4 swivel wheels are available inside the OXY backpack (2 of which with brake to be mounted on the front of the Module).

In the same backpack you will find the envelope containing all the hardware useful for the wheels and for the customization of the module through the installation of further future trays and accessories.

Wheel mounting:

- Remove the bag with wheels from the Oxy backpack
- Open the bag of screws and remove: 16 M6 screws + 16 M6 blind nuts + 32 washers
- Prepare all the screws with the washers inserted
- Remove the MODULO superstructure and tilt the trolley by resting the side where the extension holder is positioned.
- First place the wheel with brake in the front seat (towards the drawers), insert the screws with washers
- Lock the screws with the blind nuts, not before inserting the upper washer
- Perform the same procedure for the rear wheel
- Raise the trolley and rest the opposite side
- Repeat step 5, 6, 7
- Raise the trolley and make sure that the wheels slide and rotate correctly
- Tighten all screws with REASONABLE force





MODULE IS COMPOSED OF TWO DIVISIBLE ELEMENTS



Large work surface that can be used to constrain components to be coated



Housing Storm Tank

Click System OXY




Maxi paper roll




Plates for Hulk Magnets

Hook dedicated to the infrared lamp, present on the base and on the superstructure



Fractional and modular drawers



Cable holder and extension cables



Orbital support with compartment for electric cable

Coupling sprayers

Interchangeable trays also suitable for primers and sealants

Roll holder plate for masking and for knife less

Storm Tank tube rear outlet

Lower hook for Infrared Lamp

Large tank for products





Large rear product tank



Support polishers, orbitals.
Currently available as an accessory
Not supplied with MODULO!



heat gun housing



Buffers and polishing cloths

Infrared lamp attachment on upper hook

Prepared for housing industrial socket and multi-socket 220V.

